

INSPECTION LAMP/MAGNIFIER SUPER LUMINOVA

Bringing inspections into the light of day

THE SUPERLUMINOVA INSPECTION LAMP/MAGNIFIER ENABLES YOU TO VIEW LUMINESCENT MATERIALS IN DAYLIGHT

This lamp avoids the need to restrict quality inspections to a dark room. It is equipped with two different lighting systems: white light and UV light, with 3 levels of intensity.

The 2x lens lets you see a complete watch head in detail.

This wireless device can be recharged via a transformer, thus making it easier to use.

It is possible to mount a mobile phone, using a specially designed holder, to take photos.



Technical specifications:

- 2x magnifier
- 3 levels of white light
 - 2450 lux
 - 4500 lux
 - 9250 lux
- 3 levels of UV light
 - 3.75 mW/cm2
 - 6.50 mW/cm2
 - 13.50 mW/cm2

Size:

290 x 125 x 40 mm

Weight:

350 grams

References:

G414000

Content: suitcase; inspection lamp; power supply; universal phone holder





INSPECTION LAMP/MAGNIFIER SUPER LUMINOVA

Product details



RECOMMENDATIONS:

To check the intensity or uniformity of luminescent materials, you need only apply a continuous inspection at your preferred UV intensity.

If however you are trying to assess the Superluminova's colour or fading, then you will need to use UV at full power for a few seconds, and then switch off.

Our "contrast filter" accessory provides a better contrast, so that you can see only luminescent materials. It is mounted by means of a ¼-turn under the lens. (not supplied as standard)

To clean the lens, use the microfibre cloth provided. Be sure to take care of this cloth: it must always remain clean, or you could scratch the synthetic lens.

SOME EXAMPLES OF APPLICATION:

Luminescent materials Highlighting dust Seeing UV-sensitive oils



WHITE LIGHT



UV LIGHT





UNIVERSAL PHONE HOLDER:

Universal support for shooting





INSPECTION LAMP/MAGNIFIER SUPER LUMINOVA


Accessories

SUPPORT FLEXIBLE G414000-P:

For continuous control work, it is convenient to mount the lamp on a control table or on a watchmaker's bench. With its flexible hose, you can easily adjust the location and height of the lamp, or even shift it when you no longer need it.

The base is mounted on a clamp. Clamping range from 0 to 50 mm (G414000-P050) or 50 to 120 mm (G414000-P120).







	Products	References
0	Contrast filter	G414000-F
	Flexible support for workbench Fixation on support from 0 to 50 mm thickness	G414000-P050
	Flexible support for workbench Fixation on support from 50 to 120 mm thickness	G414000-P120

