

# **Manipulator stylus**

Non-marking Ref.: H491000

## THIS STYLUS PROVIDES A REVOLUTIONARY GRIP ON THIN AND DELICATE COMPONENTS

Utra-light and easy to handle, this stylus enables you to manipulate all sorts of components. It will be particularly welcome for picking up delicate components that are hard to grip with tweezers. Since it does not exert any clamping pressure, you can be sure that this tool will not scratch or deform the most delicate components.

It comprises a Ø 3 and Ø 6 end-piece made from a soft, adhesive material, without leaving any marks on the contact surfaces. This adhesive material will retain any dust present on the components. Simply run under clean water or clean using an alcohol-soaked cloth, and then dry in the open air, to restore the optimum adhesion of these end-pieces.

In case of wear, it is relatively easy to turn the end-pieces around, or replace them with new ones, so that you can restore optimal working conditions. There are caps for keeping the end-pieces clean when the stylus is not in use. The end-piece size is marked visually. Size: With caps: Ø 10 x 155 mm **Technical specifications:** Without cap: Ø 10 x 110 mm • 2 end-pieces: Ø 3 / Ø 6 mm • End-piece material: Weight: Polyurethane 0 15 grams 0 Hardness 15 Shore A **Reference:** H491000 



Route de la Jaluse 5b, 2400 Le Locle Tel : 032 926 19 46 www.techniwatch.ch





## **Manipulator stylus**

Product details



#### **XAMPLES OF APPLICATIONS:**

## **GRIPPING COMPONENTS:**

<u>The Ø3 end-piece</u> on the stylus is used for picking up small, lightweight and very delicate components

<u>The Ø6 end-piece</u> on the stylus is used for picking up relatively large and heavy components. However, the contact surface must be approximately equal to that on the end-piece.

## **REMOVING DUST / PARTICLES:**

This tool makes removing dust easy. Thanks to its cleanability, it has a long lifetime, hence it can replace disposable products.




#### **Techniwatch SA**

Route de la Jaluse 5b, 2400 Le Locle Tel : 032 926 19 46 www.techniwatch.ch











#### **Techniwatch SA**

Route de la Jaluse 5b, 2400 Le Locle Tel : 032 926 19 46 www.techniwatch.ch